MULTISMART™ ARM

FLEXIBLE EXTRACTION ARM

Flexible arm with an external balance mechanism. The parallelogram system, along with the gas springs, ensure smooth movement and exact positioning of the arm.

The MultiSmart Arm comes in three different diameters and two lengths. It has been designed for intensive use.



APPLICATIONS

The MultiSmart Arm is intended to be used for the following applications:

- MIG-MAG/GMAW welding
- TIG welding
- FCAW welding
- stick/MMAW welding

SPECIFICATIONS

Physical dimensions and properties						
Material:						
• tubes	• aluminium					
• hood	 sheet metal 					
• hoses	PVC with spring steel wire					
Colour:						
• tubes	• yellow RAL 1004					
 hood + hoses 	• black					
Ambient and process conditions						
Process temperature:						
• min.	• 5°C (41°F)					
• nom.	• 20°C (68°F)					
• max.	• 70°C (158°F)					
Max. relative humidity	90%					
Outdoor use allowed	no					
Storage conditions	• 5-45°C (41-113°F)					
	• relative humidity max. 90%					
Product combinations	5					
FUA-1800 FUA-2100	extraction fan					
Scope of supply						
Order information						
Number/package	1					
Shipping data						
Harmonized Tariff Code	84219990					
L						

MOUNTING POSSIBILITIES



PRESSURE DROP



clean air at work

Remaining specifications

PLYM[®]VENT[®]

	MSA-125/3	MSA-125/4	MSA-160/3	MSA-160/4	MSA-200/3	MSA-200/4
Physical dime	ensions and prop	erties		1		1
Diameter	Ø 125 mm (4.9 in.)		Ø 160 mm (6.3 in.)		Ø 200 mm (7.9 in.)	
Hood opening	Ø 253 mm (10.0 in.)		Ø 288 mm (11.3 in.)		Ø 328 mm (12.9 in.)	
Length	3 m (9.8 ft)	4 m (13.1 ft)	3 m (9.8 ft)	4 m (13.1 ft)	3 m (9.8 ft)	4 m (13.1 ft)
Weight (net)	22,5 kg (50 lbs.)	27,5 kg (61 lbs.)	23,5 kg (52 lbs.)	29 kg (64 lbs.)	24,5 kg (54 lbs.)	30,5 kg (67 lbs.)
Performance						
Max. airflow	400-700 m ³ /h (240-410 CFM)		800-1400 m ³ /h (470-820 CFM)		1300-2000 m ³ /h (770-1180 CFM)	
Options and a	accessories					
Extension	SAE-125/4	-	SAE-160/4	-	SAE-200/4	-
Stanchion: • 1,1 m • 2,2 m	PA-110 PA-220		PA-110 PA-220		PA-110 PA-220	
Manual on/off switch, hood- mounted	S-100		S-100		S-100	
Manual on/off switch, incl. LED working light	LL-5.5/24-125		LL-5.5/24-160		LL-5.5/24-200	
Shut-off damper	DAMPER-125		DAMPER-160		DAMPER-200	
Product com	binations					
Extraction fan	FUA-1800		FUA-1800 FUA-2100		FUA-2100 FUA-3000	
Fan mounting bracket	MB-FUA/S1		MB-FUA/S1		MB-FUA/S1 (FUA-2100) MB-FUA/S2 (FUA-3000)	
Order inform	ation					
Art. no.	0000101211	0000101214	0000101212	0000101215	0000101213	0000101216
Alternatively: MSA+SAE		0000101211 0000101253		0000101212 0000101254		0000101213 0000101255
Shipping data	a					
Gross weight						
Packing dimensions (L x W x H)						
Harmonized Tariff Code	84219990		84219990		84219990	

FEATURES & BENEFITS





Manual on/off switch on the hood, incl. LED working light (option)



Application restrictions

Do not use the product for the following applications or in the following circumstances: polishing applications in combination with grinding, welding or any other application that generate sparks (fibres from polishing or abrasive flap disks are highly flammable and pose a high risk of filter fires when exposed to sparks) | aluminium laser cutting | oil mist | heavy oil mist in welding fume | arc-air gouging | extraction of aggressive fumes and gases (e.g. from acids, from alkaline, from soldering paste containing lithium) | extraction of hot gases (more than 70°C/158°F continuously) | grinding aluminum and magnesium | flame spraying | extraction of cement, saw dust, wood dust etc. | sucking cigarettes, cigars, oiled tissues and other burning particles, objects and acids | explosive environments or explosive substances/gases

Product type Article no. Product category Version

MultiSmart Arm

refer to Order information extraction arms 160221/G

Always check the latest version on **www.plymovent.com**